

KEN BEDPAN WASHER DISINFECTOR 731

Intelligent Disinfection

- CLEAN, LEAN & GREEN

- ✓ Icons on display
- ✓ Total disinfecting system
- ✓ Easy to service access
- ✓ Complies with 15883

BWD 731 has been developed for hospital wards, isolation wards and nursing homes and with its compact design it has a small footprint.

The BWD 731 is easy to operate by touch panel with icons showing all relevant information of the program needed by the operators.

The machine is functional as a free standing, wall hung or undercounter model.

The different bedpan holders are suitable for all types of bedpan. The capacity of BWD731 is one bedpan or two urinal bottles. Most holders will be able to hold various commodes and urine measuring glasses.

A special utensils basket is available for washing kidney bowls, scissors, bowls and other small items.

All data from the BWD 731 are fully exchangeable with common computer systems.





All KEN machines conform to present EU directives, and all the hospital machines have been constructed in accordance with EN ISO 15883.

Advantages:

- Easy to use icons
- 5 standard programs - with options for 3 more
- Total disinfection guarantee
- Quick-start - automatic closing of door and automatic programme start
- Door suitable as slopsink - bedpan is emptied automatically
- Service access from the front / top
- A0 programmable

Hygiene safety

- EN 62366 tested
- EN ISO 15883-1-2-5

Environment

- Low energy costs
- Low noise level
- Low chemical usage

Technical description	Values
Outer dimensions / +plinth	H: 855/1150 x W: 450 x D: 555 mm
Operative chamber dimensions	H: 450 x W: 380 x D: 280 mm
Weight excl./incl. packaging	64/82 kg / + plinth 69/87 kg
Built in combitank	10 L
Built in detergent cabinet	5 L
Capacity bedpan / urinal bottles / bowls	1 pcs / 2 pcs / 1 pcs at a time
Cycle time, standard	35-45 min. (fast cycle machine <30 min.)
Sealing class /	IP 21 / IP 44 as option
Water connections	2 x 3/4
Cold water	200-800kPa, ≥15L7min, 5-30°, 0-30° dH
Hot water	200-800kPa, ≥15L7min, 30-70°, 0-3° dH
Bedpan program hot water	7 min.
Sound pressure ISO 11204 L	47.5 dB(A)
Water consumption per phase	See technical manual
Power supply options	3x200-415 V- 50/60 Hz
Heating elements in combitank	2x3 kW/3x3 kW
Programs available	5 standard + 3 optional
Drain	ø90 mm

Contact a KEN partner

Clean, Lean & Green